Wamix-Touch: The high-capacity and maintenance-free vacuum pump and the speed regulation of the mixer unit makes the Classic well-suited to all kinds of plaster, embedding compounds and silicones. Depending on the application three vacuum levels are adjustable. Since it just requires a single power supply connection, the selection of the location is very flexible.

Wamix-Touch Injector: It is extremely well-suited for mixing gypsums. Vacuum is achieved rapidly with this process even for large volumes, thus saving time. Another advantage is the robustness of the maintenance-free vacuum generator. Compressed air supply is required.



Wamix-Touch / Wamix-Touch Injector, wall fastening



Touch screen for fast and easy operation

### **MADE IN GERMANY**

Wassermann is a medium-sized, owner-operated company with head office in Hamburg. We design and produce high-quality technical devices in Germany. Our main users are dental laboratories, dental clinics and various industrial areas worldwide

## Why a Wassermann product?

Wassermann products are manufactured from high-quality materials and the proportion of plastics used is intentionally kept as low as possible. Our devices are known for their suitability for daily use, functionality and longevity. As a result, the users place high levels of trust in the Wassermann brand. We feel it is our duty to support our customers on a daily basis when it comes to safety, service and productivity. Technological perfection, optimum quality and especially


sustainability are the benchmarks we set. Thanks to the combination of these values. the family-owned company, since its establishment in 1927, has gained worldwide recognition as a manufacturer of high-quality products.







Further information are available on our website at www.wassermann.hamburg





## **Wamix-Touch and Wamix-Touch Injector**



**Vacuum Mixers** 



Wassermann Dental-Maschinen GmbH Rudorffweg 15–17 · 21031 Hamburg · Germany Phone: +49 (0)40 730 926-0 · Fax: +49 (0)40 730 37 24 info@wassermann-dental.com · www.wassermann.hamburg

# Vacuum Mixers

# Wamix-Touch & Wamix-Touch Injector

High value metal components, almost maintenance-free WILLIASSERMENT Visual and audible signal at programme end Visual safety system helps to identify overfilling, additionally with protective filter against taking up liquids Can be installed flexibly as a wall or counter device, table stand available as extras Simple cleaning due to stay-clean surfaces, plastic powder coated

The Wamix-mixers by Wassermann impress with their perfect and bubble free results. They are easy to operate and extremely robust, which makes work much easier for sure. A touch screen and the newly developed control panel allow the user to set the relevant parameters quickly and easily using self-explanatory symbols. The technological highlights of the Wamix Series provide the foundation for first class products - quick and reproducible.

Quick and reproducible processes: You can save 30 programs with your choice of names and access them at any timen

Beaker vented only after confirmation, post-vacuum also reduces gas inclusions

Inclined motor for easy insertion of the mixer beaker, comfortable single-hand operation, optimum mixing results

Automatic mixing when beaker is applied, programmable pre-mixing mode with right and left operation, adjustable change of rotation direction

### **Major Features**

- Innovative: The vacuum and speed values set by the user are operated by a microcontroller and are automatically readjusted
- Reproducibility at the push of a button: Vacuum and speed monitoring guarantee homogeneous mixing of all kinds of plaster, embedding materials and silicones
- Included in delivery:

Beaker, medium cpl. 350 ml Mounting set for wall fastening Compressed air hose, 2 m Wamix-Touch Injector

Accessories	Item no.
Table stand (W 219 x H 467 x D 308 mm)	171744
Beaker, extra small cpl. 75 ml	171295
Beaker, small cpl. 200 ml	171230
Beaker, medium cpl. 350 ml	171283
Beaker, large cpl. 600 m	171237
Beaker, extra large cpl.1000 ml	171269
Vacuum washing beaker, 600 ml	171275
Compressed air hose per meter Wamix-Touch Injector	320026

Wamix-Touch Wamix-Touch Injector	Item no. 171970 Item no. 171971
Voltage	220-240 V / 50/60 Hz
Power consumption max. Wamix-Touch	2.5 A (Si 4,0 A)
Power consumption max. Wamix-Touch Injector	1.8 A (Si 4,0 A)
Output Wamix-Touch	200 W
Output Wamix-Touch Injector	120 W
Speed (Motor control with intelligent regulation)	100 - 550 min <sup>-1</sup>
Vacuum <b>Wamix-Touch</b>	approx. 120 mbar (absolut)
Vacuum Wamix-Touch Injector	approx. 100 mbar (absolut)
Mixing time	999 sec. adjustable
WxHxD	195 x 310 x 180 mm
Weight <b>Wamix-Touch</b>	9.3 kg
Weight Wamix-Touch Injector	7.5 kg
Sound level	≤ 80 dB (A)
Safety class	IP 22
Compressed air connection Wamix-Touch Injector	min. 5 bar