



HSS-AZ, rear side





HSS-ZA, in the rear with polishing spindle and convenient deposit table made of stainless steel



Wassermann is a medium-sized, owner-operated company with head office in Hamburg. We design and produce high-quality technical devices in Germany. Our main users are dental laboratories, dental clinics and various industrial areas worldwide.

Why a Wassermann product?

Wassermann products are manufactured from high-quality materials and the proportion of plastics used is intentionally kept as low as possible. Our devices are known for their suitability for daily use, functionality and longevity. As a result, the users place high levels of trust in the Wassermann brand. We feel it is our duty to support our customers on a daily basis when it comes to safety, service and productivity. Technological perfection, optimum quality and especially

sustainability are the benchmarks we set. Thanks to the combination of these values. the family-owned company, since its establishment in 1927, has gained worldwide recognition as a manufacturer of high-quality products.





HSS-ZA, polishing trough with or without extractor nozzle, available as accessory



HSS-AZ/-ZA, inclined support (removable)



Further information are available onwww.wassermann.hamburg Further information are available on our website at

Your Dental Dealer



HSS-AZ and HSS-ZA



Trimmer



Wassermann Dental-Maschinen GmbH Rudorffweg 15–17 · 21031 Hamburg · Germany Phone: +49 (0)40 730 926-0 · Fax: +49 (0)40 730 37 24 info@wassermann-dental.com · www.wassermann.hamburg

Trimmer HSS-AZ & HSS-ZA

Perfect grinding in the smallest space: Whether it's the powerful **HSS-AZ** wet trimmer or the **HSS-ZA** combination trimmer with additional polishing spindle - excellent results guaranteed for dental models, thanks to their powerful motors and the almost wear- and maintenance-free technology used. The outer housing cools the motor so there is no risk of dirt entering. And of course both units are low-noise and vibration-free.

Major Features

- Highest grinding and polishing speeds HSS-AZ: 3000 min⁻¹, HSS-ZA: 2 settings, 1500 and 3000 min⁻¹
- Splash-protected as per IP 54
- HSS-AZ equipped as standard with solenoid valve for automatic water supply
- Included in delivery:
- Inclined support Supply hose, 1 m Discharge hose, 1 m Brush spindle left, 92 mm, **HSS-ZA**

Accessories	ltem no.
Spare Dia-Quick grinding disc (partially diamond coated), incl. grease	162063
Spare foil grinding disc, 1set = 4 pieces, incl. grease	162013
Spare foil grinding disc, fine, 1 set = 4 pieces, incl. grease	162023
Sealing grease for trimmer, 25 ml	629002
Puller for grinding disc change	164026
Polishing trough with extractor nozzle HSS-ZA	143130
Polishing trough without extractor nozzle HSS-ZA	143140
Polishing trough base complete HSS-ZA	161115
Brush spindle left, 92 mm, HSS-ZA	152025
Brush spindle left, 125 mm, HSS-ZA	152044
HSS-AZ incl. Dia-Quick grinding disc HSS-ZA incl. Dia-Quick grinding disc HSS-AZ incl. foil grinding disc HSS-ZA incl. foil grinding disc	ltem no. 162997 ltem no. 161996 ltem no. 162996 ltem no. 161997
HSS-ZA incl. Dia-Quick grinding disc HSS-AZ incl. foil grinding disc	ltem no. 161996 ltem no. 162996
HSS-ZA incl. Dia-Quick grinding disc HSS-AZ incl. foil grinding disc HSS-ZA incl. foil grinding disc	ltem no. 161996 ltem no. 162996 ltem no. 161997
HSS-ZA incl. Dia-Quick grinding disc HSS-AZ incl. foil grinding disc HSS-ZA incl. foil grinding disc Voltage	ltem no. 161996 ltem no. 162996 ltem no. 161997 220–240 V / 50/60 Hz
HSS-ZA incl. Dia-Quick grinding disc HSS-AZ incl. foil grinding disc HSS-ZA incl. foil grinding disc Voltage Power consumption HSS-AZ, HSS-ZA	Item no. 161996 Item no. 162996 Item no. 161997 220–240 V / 50/60 Hz 3.0 A, 3.5 A
HSS-ZA incl. Dia-Quick grinding disc HSS-AZ incl. foil grinding disc HSS-ZA incl. foil grinding disc Voltage Power consumption HSS-AZ, HSS-ZA Output	Item no. 161996 Item no. 162996 Item no. 161997 220–240 V / 50/60 Hz 3.0 A, 3.5 A 750 W
HSS-ZA incl. Dia-Quick grinding disc HSS-AZ incl. foil grinding disc HSS-ZA incl. foil grinding disc Voltage Power consumption HSS-AZ, HSS-ZA Output W x H x D HSS-AZ	ltem no. 161996 ltem no. 162996 ltem no. 161997 220–240 V / 50/60 Hz 3.0 A, 3.5 A 750 W 290 x 320 x 380 mm
HSS-ZA incl. Dia-Quick grinding disc HSS-AZ incl. foil grinding disc HSS-ZA incl. foil grinding disc Voltage Power consumption HSS-AZ, HSS-ZA Output W x H x D HSS-AZ W x H x D / D incl. spindle HSS-ZA	ltem no. 161996 ltem no. 162996 ltem no. 161997 220–240 V / 50/60 Hz 3.0 A, 3.5 A 750 W 290 x 320 x 380 mm 300 x 315 x 480 / 525 mm
HSS-ZA incl. Dia-Quick grinding disc HSS-AZ incl. foil grinding disc HSS-ZA incl. foil grinding disc Voltage Power consumption HSS-AZ, HSS-ZA Output W x H x D HSS-AZ W x H x D / D incl. spindle HSS-ZA Spindle height HSS-ZA	Item no. 161996 Item no. 162996 Item no. 161997 220–240 V / 50/60 Hz 3.0 A, 3.5 A 750 W 290 x 320 x 380 mm 300 x 315 x 480 / 525 mm 170 mm
HSS-ZA incl. Dia-Quick grinding disc HSS-AZ incl. foil grinding disc HSS-ZA incl. foil grinding disc Voltage Power consumption HSS-AZ, HSS-ZA Output W x H x D HSS-AZ W x H x D / D incl. spindle HSS-ZA Spindle height HSS-ZA Weight incl. foil grinding disc HSS-AZ, HSS-ZA	Item no. 161996 Item no. 162996 Item no. 161997 220–240 V / 50/60 Hz 3.0 A, 3.5 A 750 W 290 x 320 x 380 mm 300 x 315 x 480 / 525 mm 170 mm 19.2 kg, 19.6 kg
HSS-ZA incl. Dia-Quick grinding disc HSS-AZ incl. foil grinding disc HSS-ZA incl. foil grinding disc Voltage Power consumption HSS-AZ, HSS-ZA Output W x H x D HSS-AZ W x H x D / D incl. spindle HSS-ZA Spindle height HSS-ZA Weight incl. foil grinding disc HSS-AZ, HSS-ZA Sound level	Item no. 161996 Item no. 162996 Item no. 161997 220-240 V / 50/60 Hz 3.0 A, 3.5 A 750 W 290 x 320 x 380 mm 300 x 315 x 480 / 525 mm 170 mm 19.2 kg, 19.6 kg ≤ 70 dB (A)

